

Features

- DIN 863 IP54
- Size range from 6-8mm, 8-10mm, 10-12mm, 12-16mm, 16-20mm, 20-25mm, 25mm-30, 30-40mm and 40-50mm
- 3 Point Ensures self centering in the Bore
- Supplied in fitted case with setting ring and adjusting tools.

RS PRO Electronic 3-Point Bore Micrometers, Range from 6-8mm, 8-10mm, 10-12mm, 12-16mm, 16-20mm, 20-25mm, 25mm-30, 30-40mm and 40-50mm

RS Stock No.: 0728619



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO Electronic Bore Micrometers

RS PRO 3-point internal electronic micrometers are used to measure the internal diameter of holes, bores or cylinders with very high accuracy.

Product Features

- Measurement can be taken close to the bottom of a blind hole.
- Carbide tipped contact points (except 6-12mm).
- Ratchet stop and supplied with setting ring.
- Size range is from 6mm to 50mm.
- IP54

MAIN USES:

To measure the internal diameters of holes, bores and cylinders.

APPLICATIONS:

Engine cylinders, bushings, bearings, tubes and precision-machine holes.

General Specifications

Type	Electronic Bore Micrometers
Range Size	See details below
Length (L1)	See details below
Height	See details below
Extension Size	See details below
Ring Size	See details below
Accuracy	See details below

Stock No.	Range Size	Length (L1)	Height (A)	Extension Size	Ring Size	Accuracy
xxx-xxxx 0728619	6-8mm	54.5mm	1.5mm	100mm	6mm	0.004mm
xxx-xxxx 0728620	8-10mm	54.5mm	1.5mm	100mm	8mm	0.004mm
xxx-xxxx 0728621	10-12mm	54.5mm	1.5mm	100mm	10mm	0.004mm
xxx-xxxx 0728622	12-16mm	80.0mm	0.5mm	150mm	16mm	0.004mm
xxx-xxxx 0728623	16-20mm	80.0mm	0.5mm	150mm	16mm	0.004mm
Stock No.	Range Size	Length (L1)	Height (A)	Extension Size	Ring Size	Accuracy
xxx-xxxx	20-25mm	90.0mm	0.5mm	150mm	25mm	0.004mm

0728624						
xxx-xxxx 0728625	25-30mm	90.0mm	0.5mm	150mm	25mm	0.004mm
xxx-xxxx 0728626	30-40mm	97.0mm	0.5mm	150mm	40mm	0.004mm
xxx-xxxx 0728627	40-50mm	97.0mm	0.5mm	150mm	40mm	0.005mm

Approvals

Declarations	REACH DoC
Product Standard	EN61326-1:2013
Certification	CE, RoHS

Similar Products

Stock No.	Brand	Product Name	Size	Extension	Ring	Accuracy
xxx-xxxx 0728619	RS PRO	Electronic bore micrometers	6-8mm	100mm	6mm	0.004mm
xxx-xxxx 0728620	RS PRO	Electronic bore micrometers	8-10mm	100mm	8mm	0.004mm
xxx-xxxx 0728621	RS PRO	Electronic bore micrometers	10-12mm	100mm	10mm	0.004mm
xxx-xxxx 0728622	RS PRO	Electronic bore micrometers	12-16mm	150mm	16mm	0.004mm
xxx-xxxx 0728623	RS PRO	Electronic bore micrometers	16-20mm	150mm	16mm	0.004mm
xxx-xxxx 0728624	RS PRO	Electronic bore micrometers	20-25mm	150mm	25mm	0.004mm
xxx-xxxx 0728625	RS PRO	Electronic bore micrometers	25-30mm	150mm	25mm	0.004mm
xxx-xxxx 0728626	RS PRO	Electronic bore micrometers	30-40mm	150mm	40mm	0.004mm
xxx-xxxx 0728627	RS PRO	Electronic bore micrometers	40-50mm	150mm	40mm	0.005mm

