

Product specifications **171BV**

Last update: 12/5/2012 11:56:09 AM

General

Description	Dunlop Protomastor safety
Upper/Sole Color	White/Green
Status	Stock,
Segment	Food
Product line	
Sizerange/#	36-48/13
Hangtag	
Insole	
Lining	White polyester
Resistance code	4



171BV

Safety

Standard	EN ISO 20345:2011.SB.E.FO.SRA
	<input checked="" type="checkbox"/> Steel Toecap <input type="checkbox"/> Antistatic
	<input type="checkbox"/> Steel Midsole <input checked="" type="checkbox"/> Energy absorbing
	<input checked="" type="checkbox"/> Oilresistant sole <input type="checkbox"/> Cold insulating
Safety marking Manual	EN manual printed on polybag

Sole info

Sizing	<input checked="" type="checkbox"/> French <input checked="" type="checkbox"/> English <input type="checkbox"/> U.S.
Date of manufacturing	<input checked="" type="checkbox"/>
Other sole info	Planeta Plasticos Made in Portugal

Labeling/marketing

Marking	Dunlop stamp
Barcode on boot	Barcode label
Barcode packaging	Dunlop label
Barcode outercarton	Dunlop label

Remark

Weight 42: 2,22 kg/pr Certification updated Dec 2012

Packaging		Polybag						
Size	Boxtype	Length	Width	Height	Pairs/Box	Boxes/layer	#Layers	Pallet height
43-45	PT3	390	390	400	6	6	4	1.75
36-37	PT1	390	390	280	6	6	6	1.83
46-48	PT4	390	390	430	6	6	4	1.8
38-42	PT2	390	390	360	6	6	5	1.95