

INSULATED LONG NOSE PLIER BENT 210MM



- Approved for live working up to 1,000 volts
- Long straight jaws for easier access
- Jaws with a serrated grip for increased gripping power
- Chrome molybdenum alloy steel for durability and strength
- 80° cutting edge angle
- TPR grip for a more secure and comfortable grip
- Designed and manufactured to DIN5745 and IEC60900

Insulated Bent Long Nose Plier 8"

General information

Country of origin: Taiwan
Barcode: 5020385072091
Tarriff code Europe: 8203200000
ECCN US: EAR99
ETIM: EC000833
UNSPSC: 27112128

Dimensions

Net weight (g): 197
Length: 210 mm
Length 2: 8"

Attributes

Product type: Insulated Pliers
Material: Cr-Mo
Certificates: VDE
Handle type: TPR
Cutting capacity piano wire (mm): 1
Cutting capacity hard wire (mm): 1.5
Cutting capacity medium hard wire (mm): 2.5
Tethering facility: No
Insulated: Yes

Features



 **DESIGNED IN SWEDEN**

TengTools is a Swedish company present in more than 30 markets worldwide, and offers hand tools in smart storage solutions for demanding professionals within the automotive, maintenance and engineering sectors, as well as motor sport enthusiasts who aspire to use the same tools as top mechanics across the globe.

Technical changes and errors may occur. 01-08-2024 19:59



Sandbergsvägen 3
441 39 Alingsås, Sweden

ADDITIONAL IMAGES



WWW.TENGOOLS.COM