



tesa® 4287 EU PV11

Product Information

tesa® 4287EU General Purpose Strapping Tape



Product Description

tesa® 4287 is a general purpose strapping tape with tensilized polypropylene backing and rubber adhesive to provide good initial tack and is ideal for slightly rough surfaces due to higher adhesive coat weights. The mono-oriented polypropylene backing exhibits high conformability, good tensile strength, and low elongation. With effortless dispensing, our tape accommodates both manual and automatic operations, making it the go-to choice for streamlined packaging processes.

Product Features

- Solvent-free adhesive
- Low elongation
- Good conformability
- Better adhesion on rough surfaces compared to PV10

Application Fields

- Lightweight bundling applications
- Palletizing
- Reinforcing and unitizing

Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Product Construction

- | | | | |
|--------------------|------------------|-------------------|--------|
| • Backing | MOPP | • Total thickness | 85 µm |
| • Type of adhesive | synthetic rubber | • Color | orange |

Product Assortment

- | | |
|--------------------|---------------------|
| • Available colors | orange, transparent |
|--------------------|---------------------|

Properties/Performance Values

- | | | | |
|-----------------------|----------|-----------------------------|-----|
| • Elongation at break | 35 % | • No discoloration | yes |
| • Tensile strength | 190 N/cm | • Residue-free removability | yes |

Adhesion to Values

- | | |
|---------|--------|
| • Steel | 6 N/cm |
|---------|--------|



tesa® 4287 EU PV11

Product Information

Disclaimer

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



For latest information on this product please visit <http://l.tesa.com/?ip=04287>