

FEATURES

- Suitable for most outside applications
- 2-wire Sensor accelerate a linear response
- Robust Temperature Detector providing responsiveness and accuracy
- Long-term stability

RS PRO Temperature Sensor - 30°C to +70°C Outside Air PT10

RS Stock No.: 813-878



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Thermistor and Pt100 type sensors in a variety of packages suitable for use with most air conditioning control systems. Different industries need different solutions to keep up with the evolving world. If humidity and temperature are in play, Humidity/Temperature Transmitter seems to capture both requirements to support many applications. Merging both strengths, the Sensor can meet the specific demands of temperature-sensitive devices.

General Specifications

| | |
|-------------------------------------|--|
| Sensing Element Type | PT100,Thermistor |
| Range of Temperatures Sensed | -10°C to 110°C |
| Maximum Temperature Sensed | 110°C |
| Minimum Temperature Sensed | -10°C |
| Application | Cleanroom monitoring, HVAC (Heating Ventilation, and Air Conditioning), Ideal for applications where space is at a premium, Use with building management systems, Home appliances, Drug industry |

Electrical Specifications

| | |
|---------------------|----|
| Cable Length | 1m |
|---------------------|----|

Mechanical Specifications

| | |
|-------------------|-------------|
| Dimensions | 130mm x 6mm |
|-------------------|-------------|

Operation Environment Specifications

| | |
|--------------------------------|----------|
| Temperature Coefficient | Positive |
|--------------------------------|----------|

Protection Category

IP Rating

IP65

