

R 15-7+E-ISK-STI



Image is for illustration purposes only. Please refer to product description.

Part number	09 15 007 3001
Specification	R 15-7+E-ISK-STI
HARTING eCatalogue	https://harting.com/09150073001

Identification

Category	Inserts
Series	R 15

Version

Termination method	Crimp termination
Gender	Male
Number of contacts	7
Details	for thermoplastic hoods / housings

Technical characteristics

Rated current	10 A
Rated voltage	250 V
Rated impulse voltage	4 kV
Pollution degree	3
Rated voltage acc. to UL	600 V
Rated voltage acc. to CSA	600 V
Insulation resistance	$>10^{10} \Omega$
Limiting temperature	-40 ... +125 °C
Mating cycles	≥ 500

Material properties

Material (insert)	Polyamide (PA)
Colour (insert)	RAL 7032 (pebble grey)



Pushing Performance
Since 1945

Material properties

Material flammability class acc. to UL 94	HB
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
	CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	10
Net weight	5.4 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140022676
eCl@ss	27440223 Contact insert for circular connectors
ETIM	EC003557
UNSPSC 24.0	39121421