

STANLEY

STANLEY FATMAX® 22" Fine Finish Saw

5-15-244



Features:

- 11 teeth per inch for a fine finish
- Teeth are precision set to generate clearance of kerf for the blade to cut on both the forward and back stroke increasing cutting efficiency by 30%
- Induction hardened teeth stay sharper twice as long
- 3 sided precision ground teeth offer razor sharp cutting edges at every stage of the stroke
- Bi-material handle screwed and ultrasonically welded for comfort and security
- Handle with marked 45° and 90° angles

Description:

The STANLEY FATMAX Fine Finish 22" Saw offers outstanding performance that is perfect for fine finish cutting. The innovative 3 sided grounded teeth with 11TPI offers razor sharp cutting edges at every stage of the stroke increasing cutting efficiency by 30%. The teeth have been induction hardened so that the teeth stay sharper for twice as long for an enhanced useable life. The saw includes an ergonomically designed bi-material handle which is screwed and ultrasonically welded, giving a more secure and comfortable feel.

Specifications	
Length	22"
Teeth	11 TPI
Handle Material	Bi-material
Cut Type	Fine Finish