



## Bottle jacks

**TL120N**

TL1...N

### SAM Outillage

10 rue Camille de RochetaillÃ©e  
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:14:04





**SAM Outillage**

10 rue Camille de RochetaillÃ©e  
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:14:04



**DESCRIPTION**

**Bottle jacks**

These bottle jacks are powerful, heavy-duty jacks, ideal for the automotive, machinery and construction industries, for a wide range of lifting and pushing applications.

Easy to use, they are available in a range of capacities to suit all your needs.

TL102N: minimum height 181 mm - maximum height 345 mm

TL104N: minimum height 194 mm - maximum height 372 mm


TL106N: minimum height 216 mm - maximum height 413 mm

TL108N: minimum height 230 mm - maximum height 457 mm

TL112N: minimum height 230 mm - maximum height 465 mm

TL120N: minimum height 242 mm - maximum height 452 mm

**SPECIFIC DATA**



Designation	20-TONS PORTABLE BOTTLE JACK
Sales reference	TL120N
Weight (kg)	9.5
C (mm)	60
D (mm)	450

**SAM Outillage**

10 rue Camille de RochetaillÃ©e  
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>



A (mm)	240
Capacity	20T
B (mm)	150
Guarantee	2

**Guarantee applied****M2 | SAM Equipment and Machine Guarantee**

Guarantee for a limited period, covering technical tools, devices and machines used under normal conditions. The length is given by the number after the letter M: 1 to 5 years

L |

[>> Find out more](#)

**SAM Outillage**

10 rue Camille de RochetaillÃ©e  
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â,-

<https://www.sam-outillage.com/>

