

# M18 RLOH600-201C

## M18™ 600 M HORIZONTAL ROTARY LASER WITH ONE-KEY™

- The ultimate tool for accurate results when leveling on the jobsite
- Easy to use, one button setup
- Manual masking shutters to prevent laser interference and laser reflection from windows
- Designed for harsh jobsite conditions, IP66 rated and withstands up to 1.5 m drops
- $\pm 5^\circ$  self levelling range for fast and accurate setup
- 600 metre working range with detector (RD600), optimised for outdoor usage
- Easy-to-read detector screen, mm/in back and front backlit display for clear visibility
- Bump alert with adjustable sensitivity to notify user when laser has been moved or bumped
- 40+ hours of run time with M18 B2 battery pack
- ONE-KEY™ tool tracking & security offers a free of charge cloud-based tracking network and inventory management platform for your tools. ONE-KEY™ also features a remote locking functionality. The reporting function delivers a complete tool activity and accuracy protocol
- Flexible battery system: works with all MILWAUKEE® M18™ batteries



### REDLITHIUM™



Laser projection	1x 360°
Max run. time with M18 B2 battery (h)	40
Accuracy at 30 m distance (+/- mm)	2.4
Standard equipment	1x RD600, detector clamp
Weight with battery pack (EPTA) (kg)	3.8 (M18 B2)
Kit included	1 x M18 B2 Battery pack, M12-18 C Charger, Kitbox
Article Number	4933493191