



Brand of NTN Group

## Technical data


### ES205G2T20

Insert bearings



Spherical outer diameter, fixing by eccentric locking collar, labyrinth seal, for high-temp. applications

#### VISUAL (S)



#### PRODUCT DEFINITION

<b>Brand</b>	SNR
<b>B - Width of Inner Ring</b>	21,4 mm
<b>B1 - Overall width Inner Ring</b>	30,9 mm
<b>B2 - Width of eccentric locking collar/nut</b>	13,5 mm
<b>C - Width of Outer Ring</b>	15 mm
<b>C1 - Distance center of OR to center of lubrication zone</b>	4,3 mm
<b>d - Shaft diameter</b>	25 mm
<b>d1 - Outer dia of eccent. Lock. collar / nut of adapter sleeve</b>	37,4 mm



**NTN Europe**

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00  
 S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072  
 SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

## PRODUCT DEFINITION

<b>D - Outer diameter of OR</b>	52 mm
<b>G - Set screw size</b>	M6x1
<b>m - Distance to set screw</b>	5 mm
<b>r - Radius Inner Ring</b>	0.6
<b>S - Distance front side/bearing centre</b>	7,5 mm
<b>f0 - Factor</b>	14
<b>SW - Wrench size</b>	3 mm

## PRODUCT PERFORMANCE

<b>C - Dynamic load rating</b>	14000000 mN
<b>C0 - Static load rating</b>	7880000 mN
<b>Operating temperature min.</b>	253,15 °K
<b>Operating temperature max.</b>	473,15 °K

## OTHER FEATURES

<b>Mass</b>	0,19 kg
<b>Recommended tightening torque for set screw</b>	5.5 N-m

## BEARING FREQUENCIES

<b>BPFO - Over rolling frequency on outer ring (60 rpm)</b>	3.58178020565553 Hz
<b>BPFI - Over rolling frequency on inner (60 rpm)</b>	5.41821979434447 Hz
<b>BSF - Over rolling frequency on rolling element (60 rpm)</b>	4.69673855838714 Hz
<b>BRF - Rotational frequency - rolling element (60 rpm)</b>	2.34836927919357 Hz
<b>FTF - Rotational frequency - cage (60 rpm)</b>	0.39797557840617 Hz

