



### Product Highlights:

- Reliable memory solution for smartphones and tablets
- Easily captures, plays back, and transfers media files, including photos, videos, and songs
- Leverages UHS-I technology with Class 10 rating and speeds up to 80MB/s<sup>1</sup>
- Two-year limited warranty

### Capacities:

#### microSDHC™

16GB  
32GB

#### microSDXC™

64GB  
128GB



## Do more with your tablet or smartphone.

Designed for your smartphone and tablet, Lexar® microSDHC™/microSDXC™ UHS-I cards make it easy to capture, playback, and transfer a large number of multimedia files, including photos, videos, and songs. The cards leverage UHS-I technology to deliver Class 10 performance for easy file transfer with speeds up to 80MB/s<sup>1</sup>. These memory solutions give you the space you need to enjoy more of your favorite multimedia on the go. Two-year limited warranty.

**Do more with your multimedia.** Lexar® microSDHC™/microSDXC™ UHS-I cards make it easy to quickly capture, play back, and transfer all your favorite media files, including videos, the highest-quality movies, photos, and songs.

**Get more from your device.** Speed rated at Class 10, these cards leverage UHS-I technology to deliver Class 10 performance for easy file transfer, giving you the speed and space you need to enjoy your favorite multimedia on the go.

**Enjoy HD video capture.** Whether you're downloading and watching HD movies on your tablet, these high-capacity cards allow you to quickly capture, play back, and transfer a large amount of the highest quality 1080p Full-HD video—making it easy to store all of your favorite movies or action video.

**Rigorously tested.** All Lexar product designs undergo extensive testing in the Lexar Quality Labs, facilities with more than 1,100 digital devices, to ensure performance, quality, compatibility, and reliability.

*For more than 20 years, Lexar has been trusted as a leading global brand of memory solutions. Our award-winning lineup includes memory cards, USB flash drives, card readers, and solid-state drives. With so many options, it's easy to find the right Lexar solution to fit your needs. Lexar products are available worldwide at major retail and e-tail stores. For more information or support, visit [www.lexar.com](http://www.lexar.com).*

<sup>1</sup> Up to 80MB/s read transfer, write speeds lower. Speeds based on internal sting. Actual performance may vary. x=150KB/s. Actual usable memory capacity may vary. 1GB equals 1 billion bytes.

[www.lexar.com](http://www.lexar.com)

©2019 All Rights Reserved. Information, products, specifications, and features are subject to change without notice. Neither Lexar nor Longsys is responsible for omissions or errors in typography or photography. Lexar, the Lexar logo, and all other Lexar trademarks are the property of Longsys Electronics (HK) Co., Ltd. or Shenzhen Longsys Electronics Co., Ltd. All other trademarks are property of their respective owners.