

DeWalt DCB612-B1

20V/60V FLEXVOLT 12.0Ah/4.0Ah BATTERY

Introduction

Get power for your most demanding jobs with these **FLEXVOLT® 20V/60V MAX* 12ah batteries**. Compatible with 20V MAX*, 60V MAX* and 120v MAX tools, these batteries feature patented technology that automatically switches voltage when you change your tools. When used with 20V MAX* tools these batteries provide up to 6x the runtime to maximize productivity on long days.

Key Features

- 12.0 Ah capacity for maximum runtime
- Compatible with 20V MAX*, 60V MAX* and 120v MAX tools
- Compatible with all 20V MAX* chargers
- 3-LED fuel gauge charge indicator
- Operates in outside temperatures down to 0°f

Specifications Table

Specification	Details
Product Type	Battery
Voltage	20V
Cordless or Corded	Cordless
Power Source	Battery
Total Number of Batteries	1
Battery Amp Hours	12Ah
Charger Included	No
Charge Time	120 min
Piece Count	1
Compatibility	20V MAX* and 60V MAX* tools
Assembled Product Length	8.1-in
Assembled Product Weight	3.4-lbs
Assembled Product Width	3.63-in
Assembled Product Height	7.75-in
Country Of Origin	Malaysia
Barcode	885911595728
Individual or Set	Individual