

5904VU/2M

Assortment of 144 tools for universal use in EVA foam trays

Universal use

		art.
	059041212	5904VU/2M

- n. 16 **42:** combination wrenches 6÷21 mm
- n. 8 **55:** double open end wrenches 6x7 - 8x9 - 10x11 - 12x13 - 14x15 - 16x17 - 18x19 - 20x22 mm
- n. 9 **96/SC9:** offset hexagon key wrenches $\odot$ 1,5 - 2 - 2,5 - 3 - 4 - 5 - 6 - 8 - 10 mm
- n. 3 **1260:** screwdrivers for slotted head screws $\bullet$ 3x75-4x100-6,5x150 mm
- n. 3 **1262:** screwdrivers for cross head Phillips® screws $\oplus$ PH0x60-PH1x80-PH2x100 mm
- n. 6 **1267TX:** drivers for Torx® head screws $\odot$ T8-T10-T15-T20-T25-T30
- n. 8 **96T:** offset hexagon key wrenches $\odot$ 2-2,5-3-4-5-6-7-8 mm
- n. 1 **920AN/125:** 1/2" wobble extension bar 125 mm
- n. 1 **920AN/250:** 1/2" wobble extension bar 250 mm
- n. 1 **920/25:** 1/2" drive universal joint
- n. 1 **920/42:** 1/2" drive sliding T-handle
- n. 1 **920/55:** 1/2" reversible ratchet $\oplus$
- n. 19 **920A:** 1/2" square drive hexagon sockets $\odot$ 10÷24 - 26 - 27 - 30 - 32 mm
- n. 1 **1084:** Heavy-duty diagonal cutting nippers ∇ 160 mm
- n. 1 **1150:** combination pliers bright chrome-plated $\equiv$ 180 mm
- n. 1 **1166:** Extra-long needle nose pliers $\bullet$ 160 mm
- n. 1 **1048N:** slip joint pliers, slip-proof PVC coated handles 250 mm
- n. 1 **1052:** self - locking pliers 240 mm
- n. 2 **35:** flat chisels, ribbed type 100 - 200 mm
- n. 1 **1370T:** mechanic's hammers 300 g
- n. 1 **1390N:** nylon face hammers, wooden shafts $\varnothing$ 35 mm
- n. 1 **1032:** circlip pliers straight, internal $\odot$ 180 mm
- n. 1 **1034:** circlip pliers bent, internal $\odot$ 170 mm
- n. 1 **1036:** circlip pliers straight, external $\bullet$ 175 mm
- n. 1 **1038:** circlip pliers bent, external $\bullet$ 175 mm
- n. 1 **VPM3:** empty foam tray
- n. 1 **1692:** measuring tape 5 m
- n. 1 **1725CR:** mini hacksaw frame
- n. 1 **1771RL:** 18 mm snap-off spare blades (10 pieces) for utility knives 1771, 1771BM, 1771HD
- n. 1 **1771:** snap - off blade utility knife 170 mm
- n. 5 **860LP:** bits for slotted head screws, coloured $\bullet$ 0,5x3 - 0,6x4,5 - 0,8x5,5 - 1x5,5 - 1,2x6,5 mm
- n. 8 **860PE:** hexagon bits for power drivers, coloured $\odot$ 2 - 2,5 - 3 - 4 - 5 - 6 - 8 - 10 mm
- n. 5 **860PH:** bits for cross head Phillips® screws, coloured $\oplus$ PH0 - PH1 - PH2 - PH3 - PH4
- n. 4 **860PZ:** bits for cross head Pozidriv® - Supadriv® screws, coloured $\oplus$ PZ1 - PZ2 - PZ3 - PZ4

