



ZARGES

Datasheet

Zarges 5 Tread 'R13' Platform Step

Stock Code. 172-1312

Specification

Aluminium stiles

Aluminium treads with R13 surface

Aluminium platform with R13 surface



Standard

New EN131 Professional

150KG Rating

RS Code	Zarges Code	Overall Length (m)	Platform Height (m)	Working Height Approx. (m)	No. of Treads inc Platform	Weight (KG)
172-1312	41638	2.15	1.33	3.35	5	10.50

Features:

Safer ascent with the highest non-slip performance thanks to R13 treads for oily and wet conditions.

80 mm deep treads with R13 surface and perforations to drain fast.

Abrasion-resistant, anodised stiles.

Maximum working heights thanks to 280mm high access.

Practical aluminium storage tray for small items and tools.

Platform made from extruded aluminium (300 mm x 250 mm) with R13 surface for safer and comfortable standing even when working for longer periods of time.

Replaceable 2-component plastic end caps ensure positioning without risk of slipping and at the same time provide firm seating in the stile.

High-strength Perlon belts prevent splay, fitted on all models of 5 rungs or more.