



Specifications:

Material: Stainless Steel 304

Article No.	Size	Qty. per pack	Article No.	Size	Qty. per pack
1750414	M3 x 0.5,1.0D	20	1750418	M8 x 1.25,1.0D	20
1750421	M3 x 0.5,1.5D	20	1750425	M8 x 1.25,1.5D	20
1750428	M3 x 0.5,2.0D	20	1750432	M8 x 1.25,2.0D	20
1750415	M4 x 0.7,1.0D	20	1750419	M10 x 1,5, 1.0D	10
1750422	M4 x 0.7,1.5D	20	1750426	M10 x 1,5, 1.5D	10
1750429	M4 x 0.7,2.0D	20	1750433	M10 x 1,5, 2.0D	10
1750416	M5 x 0.8,1.0D	20	1750420	M12 x 1,75, 1.0D	5
1750423	M5 x 0.8,1.5D	20	1750427	M12 x 1,75, 1.5D	5
1750430	M5 x	20	1750434	M12 x 1,75,	5

	0.8,2.0D			2.0D	
1750417	M6 x 1.0, 1.0D	20			
1750424	M6 x 1.0, 1.5D	20			
1750431	M6 x 1.0, 2.0D	20			

Applications:

It is suitable for repair of damaged thread and widely used in automotive applications.

Kindly note:

Thread size of this articles refer to the inside thread of the repair inserts.

For the outside thread special Threading Taps are needed.

These Threading Taps could be found in the thread repair kits as following:

917-2494: M2,5 - M6

917-2498: M3

917-2508: M4

917-2482: M4 - M10

917-2514: M5

917-2491: M5 - M12

917-2505: M6

917-2511: M8

917-2523: M10

917-2520: M12