

# suction cup ESS-40-SU

Part number: 189305

FESTO

easily interchangeable,



## Data sheet

Feature	Value
Min. workpiece radius	230 mm
Nominal size	3 mm
suction cup diameter	40 mm
suction cup volume	1.566 cm <sup>3</sup>
Position of connection	on top
Assembly position	Any
Correlation to suction-cup holder	Size 4
Suction cup shape	round flat
Operating pressure	0 ... 0.95 bar
Nominal operating pressure	-0.7 bar
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7::-]
Corrosion resistance classification CRC	1 - Low corrosion stress
Food-safe	See Supplementary material information
Ambient temperature	-20 ... 60 °C
Retention force at nominal operating pressure	69.6 N
Lateral force at nominal operating pressure	83 N
Product weight	16.3 g
Mounting type	Via vacuum port
Vacuum connection	M6
Colour	blue
Shore hardness	60 +/- 5
Material of threaded plug	Wrought aluminium alloy, nickel-plated Nickel-plated brass Galvanised and chrome-plated steel
Materials note	Free of copper and PTFE Contains PWIS substances Conforms to RoHS
Material suction cup	PUR