

# EKM 30-G-2FSH



Sample image

**Order symbol :** EKM 30-G-2FSH

**Product nr :** 3530145

**Description :** Hinged cover, PC

**Remarks :** Grey

**EAN :** 6418074010308

**El. number :**

- Finland : 3422711
- Denmark : 8212012804
- Sweden : 2538222

| Dimensions : | Height | Width | Depth |
|--------------|--------|-------|-------|
| mm :         | 380    | 190   | 30    |
| inch :       | 14.96  | 7.48  | 1.18  |

## Materials :

|                   |                      |
|-------------------|----------------------|
| Material :        | Polycarbonate        |
| Cover colour :    | RAL 7035 -light grey |
| Gasket material : | Polyurethane         |

## Temperatures :

|                               |             |
|-------------------------------|-------------|
| Temperature °C (continuous) : | -40 ... 80  |
| Temperature °F (continuous) : | -40 ... 175 |

## Ratings :

|                                   |                   |
|-----------------------------------|-------------------|
| Ingress protection (EN 60529):    | IP65;             |
| electrical_insulation :           | Totally insulated |
| UV resistance :                   | UL 746C           |
| Flammability Rating :             | UL 94 V0          |
| Glow Wire Test (IEC 695-2-1) °C : | 960C              |