

Filter mat, Extract: W: 326 mm, H: 326 mm, IP54,

Model	
product brand name	SIVACON
product designation	filter mat
type of ventilation	ventilation
fan design withdrawable fan	No
design of the product EMC version	No
General technical data	
cutout width	326 mm
cutout height	326 mm
Protection class	
protection class IP	IP54
Product details	
product component fan	No
Mechanical Design	
height	326 mm
width	326 mm
fastening method	Other
fastening method	
• 19-inch installation	No
• wall mounting	No
net weight	0.1 kg
material	plastic
ambient temperature during operation	
• minimum	-10 °C
• maximum	55 °C
Approvals Certificates	
General Product Ap- proval	other
Environment	



[Confirmation](#)

[Environmental Con-
firmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MR6000-0AM40>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8MR6000-0AM40>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MR6000-0AM40

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

