

Marshalling panel - CUC-PP-PATCHBAY



1407994

<https://www.phoenixcontact.com/gb/products/1407994>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.

Marshalling panel, type: 19" rack/fixed housing, degree of protection: IP20, material: Steel, powder-coated, connection method: Screw connection, color: light grey RAL 7035



Product Description

Marshalling distributor panel, 19", 1 RU, with 5 plastic brackets

Your advantages

- for easy cable management

Marshalling panel - CUC-PP-PATCHBAY



1407994

<https://www.phoenixcontact.com/gb/products/1407994>

Commercial Data

Item number	1407994
Packing unit	1 pc
Minimum order quantity	1 pc
Sales Key	ABNAIZ
Product Key	ABNAIZ
Catalog Page	Page 394 (C-2-2017)
GTIN	4046356788076
Weight per Piece (including packing)	378 g
Weight per Piece (excluding packing)	378 g
Customs tariff number	39269097
Country of origin	DE

Marshalling panel - CUC-PP-PATCHBAY



1407994

<https://www.phoenixcontact.com/gb/products/1407994>

Technical Data

Product properties

Type	1 HE
Product type	Data plug

Dimensions

Width	482.6 mm
Height	44.45 mm
Drill hole distance, horizontal	31.6 mm

Material specifications

Color	light grey RAL 7035
Material	Steel, galvanized
Flammability rating according to UL 94	V0
Housing surface material	Powder-coated, gray
Housing material	Steel, powder-coated

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Degree of protection	IP20
Ambient temperature (operation)	-20 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Ambient temperature (assembly)	-10 °C ... 60 °C

Marshalling panel - CUC-PP-PATCHBAY



1407994

<https://www.phoenixcontact.com/gb/products/1407994>

Classifications

ECLASS

ECLASS-9.0	27060412
ECLASS-10.0.1	27060412
ECLASS-11.0	27060412

ETIM

ETIM 8.0	EC001679
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

Marshalling panel - CUC-PP-PATCHBAY



1407994

<https://www.phoenixcontact.com/gb/products/1407994>

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Marshalling panel - CUC-PP-PATCHBAY



1407994

<https://www.phoenixcontact.com/gb/products/1407994>

Accessories

19" mounting frame

19" mounting frame - CUC-PP-FRAME-19 - 1407986

<https://www.phoenixcontact.com/gb/products/1407986>

19" panel mounting frame, empty modular distribution panel, for using 8 modules (6 x RJ45 each) with 48 connections in total, 1 HE, color similar to RAL 7035



Splice box

Splice box - FOC-SB-FRAME-19-LC:12-OM2 GY - 1418815

<https://www.phoenixcontact.com/gb/products/1418815>

Splice box, type: 19" rack patch module, degree of protection: IP20, material: Sheet steel, connection method: Splicing, housing size: 1, color: light grey RAL 7035, Ethernet



Marshalling panel - CUC-PP-PATCHBAY



1407994

<https://www.phoenixcontact.com/gb/products/1407994>

Splice box

Splice box - FOC-SB-FRAME-19-LC:24-OM2 GY - 1418816

<https://www.phoenixcontact.com/gb/products/1418816>

Splice box, type: 19" rack patch module, degree of protection: IP20, material: Sheet steel, connection method: Splicing, color: light grey RAL 7035, Ethernet



Phoenix Contact 2022 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk