



**Part Number :** [731626181](#)

**Product Description :** 4.3-10 Plug, Right-Angle, Hand Tight, Solder, for 1/2" Super Flexible Coaxial Cable, One Piece Per Carton, 50 Ohms

**Series Number :** 73162

**Status :** Active

**Product Category :** RF / Coaxial Connectors



---

## Documents & Resources

### Drawings

[731626181 sd.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

### Specifications

[PS-89675-210-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### [Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

### [Industry Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	RF / Coaxial Connectors
Series	73162
Description	4.3-10 Plug, Right-Angle, Hand Tight, Solder, for 1/2" Super Flexible Coaxial Cable, One Piece Per Carton, 50 Ohms
Application	Telecommunications/Networking
Product Name	4.3-10
Style	Cable
Type	Medium
UPC	889056703598

### Electrical

Frequency	12 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 1800 Vrms@Sea Level

### Physical

Cable Attachment	Solder
Gender	Plug
Keying to Mating Part	N/A
Net Weight	134.317/g
Orientation	Right Angle

Packaging Type	Individual Carton
Panel Mount	No
Panel Mount Method	N/A
PCB Mounting	N/A
Reverse Polar	No
Wire/Cable Type	1/2" Super Flex Coaxial

---

This document was generated on Aug 11, 2025