

Neoprene gloves, ensuring comprehensive mechanical and chemical resistance

- **Increased flexibility:** Made for heavyweight applications, AlphaTec® 09-924 black hand protection gloves possess a cotton jersey liner and an anatomical shape, which follows the contours of the hand, ensuring comfort and dexterity
- **Improved protection:** These safety gloves offer high-quality neoprene coating with an AQL of 1.5, guarding from a broad range of chemicals, including oils, acids, caustics, alcohols as well as solvents, and mechanical hazards
- **Added features:** Owing to their special Hi-Lo insulated gauntlet option with quilted cotton liner, AlphaTec® 09-924 heat and cold-resistant gloves are suitable for hot and cold conditions, as it allows intermittent handling in hot liquids up to 180°C and in cold temperatures down to -25°C



Industries

- Metal fabrication
- Chemical

Applications

- Foundry operations
- Handling materials with sharp or rough edges
- Extruding, bending and punching shapes
- Processing sheets, coils, tubes
- Fabricating metal parts, glass sheets
- Unexpected leakages spills or other releases

Previously known as: Scorpio™ 09-924

Key Features

- **Cotton jersey liner:** For comfortable and flexible work gloves
- **High-quality neoprene coating:** Broad-spectrum chemical protection
- **Hi-Lo insulated gauntlet option:** Ideal for hot and cold temperatures

Vulcanization Chemical Accelerators

- Zinc Dibutyldithiocarbamate

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.



Performance Standards



0493

EN388: 2016



3121B

EN 407



XXXXXX

EN ISO 374-5:2016



EN ISO 374-1:2016 Type A



AKLMPT

EN ISO 374-5:2016



EN 374



Specifications

BRAND STYLE	DESCRIPTION	SIZE	LENGTH	COLOR	PACKAGE
AlphaTec® 09-924	Liner Material: Cotton Jersey Coating Material: Neoprene	10	350 / 13.8	Black	12 pairs per bag, 3 bags per carton

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada Inc.
105, rue Lauder
Cowansville (Québec)
J2K 2K8, Canada
T: 1 800 363-8340
F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.