

8042EN
Lifting eye nuts, self-coloured

CE

DIN 582

TECHNICAL DATA

- safety factor: 6
- heat treatment: normalizing
- traceability code

LABORATORY TESTS

- chemical analysis
- metallographic analysis
- tensile test

AVAILABLE CERTIFICATES

- Technical product specifications
- Test report UNI EN10204 type 2.2
- Inspection certificate UNI EN10204 type 3.1
- CE Declaration of Conformity



		art.	Ø mm	$\frac{W}{L}$ mm	WLL kg	F mm
*	080420306	8042EN M6	M6	1	90	14
	080420308	8042EN M8	M8	1,25	140	20
	080420310	8042EN M10	M10	1,5	230	25
	080420312	8042EN M12	M12	1,75	340	30
*	080420314	8042EN M14	M14	2	480	30
	080420316	8042EN M16	M16	2	700	35
*	080420318	8042EN M18	M18	2,5	930	35
	080420320	8042EN M20	M20	2,5	1200	40
*	080420322	8042EN M22	M22	2,5	1450	40
	080420324	8042EN M24	M24	3	1800	50
*	080420327	8042EN M27	M27	3	2400	55
	080420330	8042EN M30	M30	3,5	3200	60
	080420336	8042EN M36	M36	4	4600	70
*	080420337	8042EN M36F	M36F	3	4600	70
	080420342	8042EN M42	M42	4,5	6300	80
*	080420343	8042EN M42F	M42F	3	6300	80
	080420348	8042EN M48	M48	5	8600	90
*	080420349	8042EN M48F	M48F	3	8600	90