



Specification Control Drawing

Raychem

a) Part as supplied.

202K1**-100





DIMENSIONS	in millimetres				
DIMENSIONS	{in inches, for reference}				

			Н	,	J	Р	R	S	Т	U&V	JO	HW	JW	Χ	Υ
	Part No.	Min	Max	Min	Max	±10%	±10%	±10%	±10%	±10%	±10%	±20%	±20%	±20%	±20%
		а	b	а	b	b	b	b	b	b	b	b	b	b	b
1)	202K121	24 {0.94}	10.4 {0.41}	14 {0.55}	5.6 {0.22}	38 {1.50}	21 {0.83}	3.0 {0.12}	1.0 {0.04}	12 {0.47}	8.5 {0.33}	1.6 {0.06}	0.9 {0.04}	24 {0,94} (2)	13 {0.51}
1)	202K132	30 {1.18}	14.2 {0.56}	15 {0.59}	5.9 {0.23}	55 {2.17}	32 {1.26}	3.0 {0.12}	1.0 {0.04}	12 {0.47}	11.5 {0.45}	1.8 {0.07}	1.0 {0.04}	24 {0.94}	18 {0.71}
1)	202K142	31 {1.22}	18.0 {0.71}	18 {0.71}	7.1 {0.28}	67 {2.64}	35 {1.38}		1.0 {0.04}	20 {0.79}	17.0 {0.67}	1.8 {0.07}	1.0 {0.04}	32 {1.26}	25 {0.98}
1)	202K153	36 {1.42}	22.4 (0.88)	21 {0.83}	8.4 {0.33}	80 {3.15}	42 {1.65}	3.0 {0.12}	1.0 {0.04}	20 {0.79}	19.5 {0.77}	2.0 {0.08}	1.0 {0.04}	32 {1.26}	30 {1.18}
	202K163	43 {1.69}	28.2 {1.11}	25 {0.98}	9.9 (0.39)	99 (3.90)	61 {2.40}	3.0 {0.12}	1.7 {0.07}	20 {0.79}	21.0 {0.83}	2.2 {0.09}	1.0 {0.04}	52 {2.05}	30 {1.18}
	202K174	52 {2.05}	35.1 {1.38}	39 {1.54}	15.7 {0.62}	130 {5.12}	72 {2.83}	3.0 {0.12}	1.7 {0.07}	20 {0.79}	39.0 {1.54}	3.2 {0.13}	1.5 {0.06}	52 {2.05}	50 {1.97}
	202K185	66 {2.60}	44.5 {1.75}	42 {1.65}	16.8 {0.66}	170 {6.69}	90 {3.54}	3.0 {0.12}	2.0 {0.08}	20 {0.79}	51.5 {2.03}	3.8 {0.15}	2.0 {0.08}	52 {2.05}	70 {2.76}

See over for explanation of Notes

Copyright (!)

The copyright in this drawing is the property of Tyco Electronics UK Ltd. The drawing is issued on the condition that it is not copied, reproduced or disclosed to a third party, either in whole or in part without the prior written consent of Tyco Electronics UK Ltd.


Drawn A.LILLEY. Checked Issue 4 Date February 2007 Conforms to ISO Recommendations
3rd Angle Projection
Not to Scale

Design MKTG. Q.A.

202K1XX-100

Raychem Specific Control				Part Number 202K1%%—100 Issue 4
Iss.	Date	E.C.R. No.	Detail	s of Change
2 3 4	December 1985 May 1990 February 2007	4502 **** CR06-HM-012		was on 2 seperate drawings dimensions added

Ordering Information



COMPATIBILITY CHART

Material Description	SPEC Number	Coating Slash Number
Zero Halogen	RT-1323, RK-6717	/86, /180
	<u> </u>	· · · · · · · · · · · · · · · · · · ·

NOTES

- (1) Supplied with 2 lips only, Dimension V does not apply.
- Potting Port X @ 90° to Potting Port Y on 202K121.
- 3 Potting Ports are optional, when specified by suffix -00 they will be located as shown.
- 4 As supplied dimensions are for uncoated parts, when coating is added entry diameters will reduce by 1.5mm Max.
- (5) If eyelet clip (000W212) is required with part then add CS-1858 to description (i.e. 202K132-100-0-CS-1858).

Tyco Electronics UK Ltd. Faraday Road, Swindon, Wiltshire, SN3 5HH England Telephone: (01793) 528171 Fax: 572516	Tyco Electronics Corporation 300, Constitution Drive, Menlo Park, CA 94025 USA Telephone (650) 361-3860 Fax: (650) 361-5579
Cage Code K1010	Cage Code 06090