

Features

- Polished Stainless Steel Scraper Blade
- Soft Grip Handles with Hanging Holes
- Suitable for a Wide Variety of Application
- 3 pc Set – Includes 32mm, 50mm, 32mm Angled Scraper
- Hammer Cap – Permits Careful Use with Hammer

RS PRO Stainless Steel Scraper, 3pcs

RS Stock No.: 0246383



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

RS PRO Stainless Steel Scraper, 3pcs

RS PRO scraper set is made by stainless steel blades which thickness of 1.0 mm. It has reinforced strike zone. It has 3 shapes - Straight with width - 32 mm, Straight with width - 50 mm and an Angled with width: 32 mm.

- 220mm (Length), 1.0mm (Thickness)
- Blade Material: Stainless Steel
- Handle – PP/TPR Grip with Metal Hammer End
- Size: 32, 50 mm and 32 mm
- 3pcs per set

General Specifications

Type	Scraper
Material	Blade- Stainless Steel Handle – PP/TPR Grip with Metal Hammer End
Number of Pieces	3
Non Sparking	No

Mechanical Specifications

Hammer Cap	Zinc Alloy
Finish -Blade	Polished
Length	220mm
Blade Width	32mm (Straight & Angled), 50mm (Straight)

Similar Products

Stock No.	Brand	Product Name	Blade Size	Blade Thickness	Handle
0246383	RS PRO	Scraper set, 3pcs	32mm, 32mm, 50mm	1.0mm	PP/TPR Grip with Metal End
0246384	RS PRO	Scraper Straight	32mm,	1.0mm	PP/TPR Grip with Metal End
0246386	RS PRO	Scraper Angle	32mm,	1.0mm	PP/TPR Grip with Metal End
0246387	RS PRO	Scraper Straight	50mm	1.18mm	PP/TPR Grip with Metal End
0246389	RS PRO	Scraper 5 in 1	75mm	1.12mm	PP/TPR Grip with Metal End