



GDX 18V-285 Impact Driver / Wrench

NO MORE CONVERTER

With a 2-in-1 GDX tool holder, you can screw drive and bolt with a single tool

LONGER SERVICE LIFE

With the brushless motor from Bosch



POWERFUL TOOL

Offering 285Nm max torque for tough jobs and 500Nm in breakaway for untightening jobs

ERGONOMIC HANDLE

Prevents fatigue thanks to ergonomic slim handle



Socket Set



Impact Bits



GAL 18V-40



2x 4.0Ah



M-Bag

1 Suitable for Various Applications: With 2-Speed selection for different applications and auto driving modes for quality finishing

2 Convenience: Single tool for both screwdriving and bolting without converters

3 Superior Torque: Soft ergonomic handle for easy and convenient operation



Description	Part No.	EAN
GDX 18V-285 + Socket Set + Impact bits (2x 4.0Ah, GAL 18V-40; M-Bag; C)	0615V00060	4053423712797

Technical Information		
Voltage	V	18
Tightening Torque	Nm	285
Maximum Nut Size	Mxx	M18
No. load Speed	rpm	0-2,800
Impact Rate	bpm	0-3,600
Head length	mm	147
Speed Selection	-	2
Motor Type	-	Brushless
Tool Dimensions (Length x Width x Height)	mm	550 x 280 x 290
Weight (excl. Battery)	kg	1.1



500 Nm



0-2800
min⁻¹/rpm



18
V



285 Nm



1/2" & 1/4"



BRUSHLESS
MOTOR



SPEED
SELECTION



Powered by **BOSCH**



¹ With online registration
www.bosch-professional.com/pro360