



ENGLISH

Datasheet

Maintenance Terminal Crimping Tool

RS Stock number [499-2313](#)



Specification

Material

- Crimping Jaw and Ratcheting Mechanism - Power die casting chrome molybdenum vanadium steel
- Body - Press molded medium steel sheet
- Automatic Return Spring, Rivets and Spring - Low carbon steel Grip - Polypropylene injection

Finish

- Crimping Jaw and Ratcheting Mechanism - Chemical blackened finish
- Body - Black electrical deposition
- Grip - Red colour

Hardness

- Crimping Jack - Heat treated to HRC: 40 ~43 degrees
- Body – Heat treated HRC: 42 ~ 48 degrees
- Rivet – Heat treated to HRC: 30 degrees up

Contents

1 Pc - Standard insulated terminal ratcheting crimping tool (suitable for use on insulated vinyl, Polycarbonate and nylon Red, Blue and Yellow. (wire range from 1.5 mm² to 6.0 mm², net weight 480 grams).