



Datasheet
COB LED 500 LM
Rechargeable Work light
with Strong Magnet

RSPRO-i3R
1766028





LED:	COB LED
Lumen:	400 Lumen
Wattage:	5W
Colour Temp:	6500k
Operating Voltage:	3.7v
IP Rating:	IPX3
Anti-Corrosive:	No

Features:

Black high-end aluminium construction
Tactical rubberised operation switch
Powered by rechargeable battery
Includes Magnetic Charging Base and Micro-USB cable plus a 'Magic' magnetic charge cable
Strong magnet on base
IPX3 Water Resistance
Pull-out Pocket clip

Dimensions: 197 x 27 x 27mm

Batteries: 3.7v 2200mAh 18650 Li-ion Rechargeable Battery

Weight: 168g torch only, 216g with battery

Switching Modes:

High ON / Red ON / Red Flash ON / OFF

ANSI FL1 Standard

Lumens: 100% White - 500 lumen / 100% Red - 45 lumen

Runtime: 100% White - 4.5H / 100% Red - 8H

Beam Range: 100% White - 37m / 100% Red - 13m