

# LabelManager™ 210D



## All-Purpose Label Maker with Large Graphical Display

- Computer-style keyboard with country-specific layout
- Prints up to 10 copies of the same label
- Create labels with 6 font sizes, 7 text styles, and 8 boxes plus underline
- Quick access buttons to punctuation / currency / other symbols / diacriticals
- Store and quickly access up to 9 frequently-used labels



### Single Unit Includes:

- LabelManager 210D Label Maker
- D1 Starter Label Cassette, Black On White 12mm x 3m
- Instruction Manual
- 2-Year Limited Warranty Card



### Kit Includes everything in single unit, plus:

- D1 Label Cassette, Black on Yellow 12mm x 3m
- Quick Reference Guide
- 6 AA batteries
- AC Adapter



Quick Specs	
Unit Dimensions (H x W x L)	155 x 165 x 64mm
Weight (excluding battery)	435 g
Mac®/PC Compatible	No
Accepts Label Sizes	6, 9 and 12mm
Tape Platform	D1, IND
Resolution	180 dpi
Printing System	Thermal Transfer
Print Speed	12mm /sec
Barcodes	No
Cutter Type	Manual
Batteries	6 AA (not included)
Adapter	Yes (optional, sold separately)
Networking	No
Country of Origin	China

Item Number	Description		Length (cm)	Width (cm)	Height (cm)	Weight (kg)	QTY	EAN	Customer Price
S0784440	LabelManager 210D QWERTY GB	Unit	9.7	22.2	20.3	0.8	1	3501170784440	
		Shelf	-	-	-	-	-	-	
		Case	61.0	23.6	22.8	5.4	6	13501170784447	
		Pallet	120.0	80.0	106.2	132.4	120	-	
Accessories (www.dymo.com)									
S0721430	AC Adapter	Unit	11.5	6.0	9.0	0.2	1	-	

LabelManager™ 210D | Compatible Labels



D1 Standard\*

For hundreds of tasks around the office or home office, such as filing, storage and asset tracking.

Temperature rating: -18°C to 90°C

\*For use with LabelManager™ series and LabelWriter™ 450 Duo

D1 Compatible Labels													
Width	Length	A	A	A	A	A	A	A	A	A	A	A	A
D1 STANDARD													
6mm	7m	S0720780	S0720770	S0720790	–	–	–	–	–	–	–	–	–
9mm	7m	S0720680	S0720670	S0720730	S0720710	S0720740	S0720720	–	–	S0720690	–	S0720700	–
12mm	7m	S0720530	S0720500	S0720580	S0720560	S0720590	S0720570	S0720600	S0720610	S0720540	S0720510	S0720550	S0720520



IND Vinyl

Ideal for both indoor and outdoor applications. Available in the widest range of colors that meet OSHA, ANSI and ISO color standards.

- UL recognized component to UL 969
- RoHS compliant
- Temperature rating: -40°C to 80°C

IND Permanent Polyester

Professional, polished finish ideal for panels, blocks, faceplates, shelves, bins, beams and more.

- UL recognized component to UL 969
- RoHS compliant
- Temperature rating: -40°C to 150°C

IND Flexible Nylon

Specifically designed for curved surfaces and wire and cable marking.

- UL recognized component to UL 969
- RoHS compliant
- Temperature rating: -10°C to 80°C

For use with LabelManager™ series and LabelWriter™ 450 Duo and Rhino™ series

IND Compatible Labels													
Width	Length	A	A	A	A	A	A	A	A	A	A	A	A
IND VINYL													
9mm	5.5m	18443	–	–	–	–	–	1805437	–	–	–	–	–
12mm	5.5m	18444	–	18432	18435	1805413	1805416	1805435	1805414	1805243	1805415	1805412	–
IND PERMANENT POLYESTER													
6mm	5.5m	1805442	1805440	–	–	1805441	–	–	–	–	–	–	–
9mm	5.5m	18482	18508DMO	–	–	18485	–	–	–	–	–	–	–
12mm	5.5m	18483	622289	–	–	18486	–	–	–	–	–	–	–
IND FLEXIBLE NYLON													
12mm	3.5m	18488	–	18490	–	–	–	–	–	–	–	–	–

Country of Origin: Belgium

DISTRIBUTED BY:  
Newell Europe Sàrl  
Chemin de Blandonnet 10  
1214 Vernier – Switzerland  
WWW.DYMO.COM



A Newell Rubbermaid Brand

This information is being provided for general information purposes and the compliance standards and certifications referenced herein are based on current standards which are subject to change.

©2014 Newell Europe LLC