



Vaste Floodlight 100W



- Modern architectural slim die-cast LED floodlight suitable for residential and commercial applications
- Die-cast construction and heat sink design providing optimised thermal characteristics for optimum LED life and performance
- Graphite textured paint finish
- Pre-wired with 1 metre of rubber insulated cable for ease of installation
- Polycarbonate spike accessory (up to 50W versions only) allowing installation into lawn and garden applications
- Non-dimmable

General Information

Lamp Type	LED
IP Rating	IP65
IK Rating	IK08
Class Protection	1
Internal / External	Internal / External
Surface / Recessed / Suspended	Surface
Warranty (Years)	5
Material	Aluminium





Technical Information

Wattage	100W
Lumens Delivered	10100lm
Lm/W	102lm/W
Beam Angle	90/100
CRI	80
CCT	4000K
Input	220/240V
Hertz	50/60Hz
Operating Temp	-20°C to 25°C
Lumen Depreciation	L70 60,000h
Power Factor	0.95



