

FI F204B+63/0,3



FI F204B+63/0,3 Residual Current Circuit Breaker



General Information

Extended Product Type	FI F204B+63/0,3
Product ID	2CSF204701R3630
EAN	8012542043225
Catalog Description	FI F204B+63/0,3 Residual Current Circuit Breaker
Long Description	FI F204B+63/0,3 RCD

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85363030

Popular Downloads

Data Sheet, Technical Information	9AKK107046A0424
Instructions and Manuals	Manual sheet inside the box

Dimensions

Product Net Width	0.070 m
Product Net Height	0.085 m
Product Net Depth / Length	0.0695 m
Product Net Weight	0.500 kg

Technical

Operating Characteristic	Instantaneous
Type of Residual Current	B+ type
Rated Residual Current	300 mA
Rated Current (I_n)	63 A
Number of Poles	4
Power Loss	2.13 W

Environmental

Ambient Air Temperature	Operation -25 ... +55 °C
-------------------------	--------------------------

Storage -40 ... +70 °C

Certificates and Declarations (Document Number)

Declaration of Conformity - CE	9AKK106713A5602
Environmental Information	Refer to RoHS
Instructions and Manuals	Manual sheet inside the box
RoHS Information	2CSC423001K2702

Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	0.073 m
Package Level 1 Height	0.078 m
Package Level 1 Depth / Length	0.090 m
Package Level 1 Gross Weight	0.525 kg
Package Level 1 EAN	8012542043225

Classifications

Object Classification Code	Q
ETIM 6	EC000003 - Residual current circuit breaker (RCCB)
ETIM 7	EC000003 - Residual current circuit breaker (RCCB)

Categories

Low Voltage Products and Systems → Modular DIN Rail Products → Residual Current Devices RCDs → Residual Current Devices RCDs

