


FEATURES

- Durable alloy 600 stainless steel sheath
- Mineral insulation for flexibility and durability
- Insulated hot junction for reduction in electrical interference

RS PRO Type K Thermocouple 100mm Length, 1mm Diameter → +800°C

RS Stock No.: 824-0603



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

These Type K thermocouple sensors feature an Alloy 600 probe sheath and are terminated with a miniature IEC flat pinned plug with a maximum temperature range of 200°C, for a quick and simple connection. The sheath of the probe is mineral insulated making it flexible, allowing it to bent and formed to suit a wide range of applications. The thermocouple has an ungrounded insulated hot junction for a reduction in electrical interference

General Specifications

Thermocouple Type	Type K
Construction	These Type K thermocouple sensors feature an Alloy 600 probe sheath and are terminated with a miniature IEC flat pinned plug
Measuring Junction	Underground
Response Time	<2 s
Application	heat exchangers, power stations, brick and cement kilns, heat treatment and annealing furnaces, thermostats, food thermometers, vehicle diagnostics and in laboratories


Mechanical Specifications


Probe Diameter	1mm
Probe Length	100mm
Probe Body Material	Inconel 600
Insulation / Sheath Material	Alloy 600
Termination Type	Miniature Plug

Approvals

a	
Standards Met	IEC







Other dimensions:

Length Diameter	100mm	150mm	250mm	500mm	1000mm
1mm	8240603	8240607	8240616	8240619	8240613
1,5mm	8240622	8240625	8240629	8240638	8240631



T/C Type	Conductors	Length	Termination	+Positiv		-Negativ tail wire		Allied Code		RS order Code
'K'	1/0.2mm	1 metre	Mini plug	Green		White		70643600		363-0250
'K'	1/0.2mm	2 metre	Mini plug	Green		White				110-4482
'K'	1/0.2mm	5 metre	Mini plug	Green		White				123-6306
'K'	1/0.2mm	10 metre	Mini plug	Green		White				123-6307
'J'	1/0.2mm	1 metre	Mini plug	Black		White		70643599		363-0244
'J' 'J'	1/0.2mm 1/0.2mm	2 metre 5 metre	Mini plug Mini plug	Black Black		White White				123-6308 123-6309
'n	1/0.2mm 1/0.2mm	10 metre	Mini plug	Black		White				123-6310
•	1/0.211111	10 metre	Willin plug	Didek		Wince				123-0310
'T'	1/0.2mm	1 metre	Mini plug	Brown		White		70643601		363-0266
'T' 'T'	1/0.2mm	2 metre	Mini plug	Brown Brown		White				123-6311
T'	1/0.2mm 1/0.2mm	5 metre 10 metre	Mini plug Mini plug	Brown		White White				123-6312 123-6313
T/C	Туре	Conductors	Cores		Reel Le	ength	Allied	l code	RS o	rder code
J		1/0.2mm	+Black/-White		25 met	res	7065	7194	827-	5980
J		1/0.2mm	+Black/-White		50 met	res	7065	7195	827-	5984
J		1/0.315mm	+Black/-White		25 met	res	7065	7198	827-	5993
j		1/0.315mm	+Black/-White		50 met		7065			5996
K		1/0.315mm	+Green/-White		25 met		7065			6000
K		1/0.315mm	+Green/-White		50 met		7065			6019
T		1/0.315mm	+Brown/-White				7065			
		•	•		25 met					6028
Т		1/0.315mm	+Brown/-White	2	50 met	res	7065	/206	82/-	6022
J		1/0.508mm	+Black/-White		25 met	res	7065	7197	827-	5990
J		1/0.508mm	+Black/-White		50 met	res	7065	7201	827-	6003
K		1/0.508mm	+Green/-White		25 met	res	7065	7203	827-	6012
K		1/0.508mm	+Green/-White	2	50 met	res	7065	7204	827-	6016
J		7/0.2mm	+Black/-White		25 met	res	7065	7202	827-	6006
K		7/0.2mm	+Green/-White		25 met		7065			6025
T		7/0.2mm	+Brown/-White		25 met		7065			6031
N		7/0.2mm	+Pink/-White	_	25 met		7065			6034
IN		//0.2111111	Trilik/-Willite		25 met	162	7003	7210	02/-	0034



	Conductors	Cores	Jacket	Reel Length	Allied Code	RS order code
Exten	sion:					
KX	7/0.2mm	+Green/-White	Green	10 metres	70657084	827-5615
KX	7/0.2mm	+Green/-White	Green	25 metres	70641729	236-3820
KX	7/0.2mm	+Green/-White	Green	50 metres	70657085	827-5619
KX	7/0.2mm	+Green/-White	Green	100 metres	70646156	611-7889
KX	7/0.2mm	+Green/-White	Green	200 metres	70657088	827-5628
JX	7/0.2mm	+Black/-White	Black	10 metres	70641640	219-4753
JX	7/0.2mm	+Black/-White	Black	25 metres	70657078	827-5592
JX	7/0.2mm	+Black/-White	Black	50 metres	70657078	827-5596
JX	7/0.2mm	+Black/-White	Black	100 metres	70637079	236-3915
JX	7/0.2mm	+Black/-White	Black	200 metres	70657081	827-5606
JA	7/0.211111	+blacky-willte	DIdCK	200 metres	70037061	827-3000
TX	7/0.2mm	+Brown/-White	Brown	10 metres	70641637	219-4703
TX	7/0.2mm	+Brown/-White	Brown	25 metres	70641734	236-3870
TX	7/0.2mm	+Brown/-White	Brown	50 metres	70657095	827-5653
TX	7/0.2mm	+Brown/-White	Brown	100 metres	70651749	762-1146
TX	7/0.2mm	+Brown/-White	Brown	200 metres	70657098	827-5662
NX	7/0.2mm	+Pink/-White	Pink	10 metres	70641635	219-4668
NX	7/0.2mm	+Pink/-White	Pink	25 metres	70657091	827-5637
NX	7/0.2mm	+Pink/-White	Pink	50 metres	70657089	827-5631
NX	7/0.2mm	+Pink/-White	Pink	100 metres	70657092	827-5640

	Conductors	Cores	Jacket	Reel Length	Allied Code	RS order code
Compensating:						
VX (KCB)	7/0.2mm	+Green/-White	Green	10 metres	70657082	827-5609
VX (KCB)	7/0.2mm	+Green/-White	Green	25 metres	70641629	219-4551
VX (KCB)	7/0.2mm	+Green/-White	Green	50 metres	70657080	827-5603
VX (KCB)	7/0.2mm	+Green/-White	Green	100 metres	70641630	219-4573
VX (KCB)	7/0.2mm	+Green/-White	Green	200 metres	70657083	827-5612
VX (KCB)	13/0.2mm	+Green/-White	Green	10 metres	70657086	827-5621
VX (KCB)	13/0.2mm	+Green/-White	Green	25 metres	70657087	827-5625
VX (KCB)	13/0.2mm	+Green/-White	Green	50 metres	70657090	827-5634
VX (KCB)	13/0.2mm	+Green/-White	Green	100 metres	70651750	762-1152
U (RCA)	7/0.2mm	+Orange/-White	Orange	10 metres	70657096	827-5656
U (RCA)	7/0.2mm	+Orange/-White	Orange	25 metres	70646158	611-7902
U (RCA)	7/0.2mm	+Orange/-White	Orange	50 metres	70657097	827-5659
U (RCA)	13/0.2mm	+Orange/-White	Orange	10 metres	70641641	219-4769
U (RCA)	13/0.2mm	+Orange/-White	Orange	25 metres	70657093	827-5643
U (RCA)	13/0.2mm	+Orange/-White	Orange	50 metres	70657094	827-5647



T/C Type	Conductors	Cores	Reel Length	Allied code	RS order code
KX	1/0.2mm	+Yellow/-Red	25 metres	70656106	814-0030
KX	1/0.2mm	+Yellow/-Red	50 metres	70656111	814-0049
KX	1/0.2mm	+Yellow/-Red	100 metres	70656109	814-0042
KX	7/0.2mm	+Yellow/-Red	25 metres	70656110	814-0046
KX	7/0.2mm	+Yellow/-Red	50 metres	70656113	814-0055
KX	7/0.2mm	+Yellow/-Red	100 metres	70656114	814-0058
KX	1/0.3mm	+Yellow/-Red	25 metres	70656104	814-0024
KX	1/0.3mm	+Yellow/-Red	50 metres	70656107	814-0033
KX	1/0.3mm	+Yellow/-Red	100 metres	70656108	814-0036
TX	1/0.3mm	+Blue/-Red	25 metres	70656121	814-0080
TX	1/0.3mm	+Blue/-Red	50 metres	70656126	814-0099
TX	1/0.3mm	+Blue/-Red	100 metres	70656124	814-0092
TX	1/0.2mm	+Blue/-Red	25 metres	70656125	814-0096
TX	1/0.2mm	+Blue/-Red	50 metres	70656128	814-0106
TX	1/0.2mm	+Blue/-Red	100 metres	70656129	814-0109

T/C Type	Conductors	Cores	Jacket	Reel Length	Allied code	RS order code		
Extension:								
KX	7/0.2mm	+Yellow/-Red	Yellow	25 m	70656102	814-0018		
KX	7/0.2mm	+Yellow/-Red	Yellow	100 m	70656105	814-0027		
KX	7/0.2mm	+Yellow/-Red	Yellow	200 m	70656103	814-0020		
JX	7/0.2mm	+ White/-Red	Black	25 m	70656096	813-9995		
JX	7/0.2mm	+ White/-Red	Black	100 m	70656098	814-0005		
JX	7/0.2mm	+ White/-Red	Black	200 m	70656099	814-0008		
TX	7/0.2mm	+Blue/-Red	Blue	25 m	70656119	814-0074		
TX	7/0.2mm	+Blue/-Red	Blue	100 m	70656122	814-0083		
TX	7/0.2mm	+Blue/-Red	Blue	200 m	70656123	814-0086		
Compensating:								
VX (KCB)	7/0.2mm	+Yellow/-Red	Yellow	25 m	70656127	814-0103		
VX (KCB)	7/0.2mm	+Yellow/-Red	Yellow	100 m	70656130	814-0112		
VX (KCB)	7/0.2mm	+Yellow/-Red	Yellow	200 m	70656131	814-0115		