

## Features

- **Universal Fit** – Compatible with single gang fused spur connection units complying with BS 1363-4 standards.
- **Tool-Free Installation** – Installs easily using existing fascia plate screw heads—no special tools required.
- **Prevents Fuse Reinsertion** – Securely blocks access to the fuse tray during maintenance for enhanced safety.
- **Durable Construction** – Made from non-conductive, metal-free polypropylene for added safety and longevity.
- **Flexible Design** – Accommodates flex outlets and has industry-standard fixing centres.
- **Supports Local Isolation** – Ideal for isolating appliances like boilers, cookers, and dryers during servicing.

## RS PRO Universal Fused Spur Lockout

RS Stock No.: 0710508



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description

- *A universal locking device designed to fit BS 1363-4 fused spur units in residential, commercial, and industrial environments.*
- *Enables safe and compliant isolation of fixed-wired appliances during maintenance, in line with the Electricity at Work Regulations.*
- *Secured in place using the screw heads of the fascia plate—prevents reinsertion of the fuse and unauthorized power restoration.*
- *Compatible with most standard lockout safety padlocks (padlocks not included).*
- *Features industry-standard fixing centres and space to allow flex cable routing.*
- *Constructed from tough, non-metallic polypropylene for safe and reliable long-term use.*

## General Specifications

Type	Wall Switch Lockout
Material	Polypropylene
Colour	Red
Padlock holes	01
Package	PE-LD

## Mechanical Specifications

Dimensions	92mm x 84mm x 29mm (excl. shackle)
Depth	29mm
Width	92mm
Height	84mm
Maximum padlock shackle diameter	6mm
Weight	34 Grams

## Operation Environment Specifications

Withstand temperature	-30°C to 80°C
-----------------------	---------------