


FEATURES

- Low cost
- Excellent insulation properties
- Flexible
- Stable, robust and durable
- Oil resistant

RS PRO 3 Core 1 mm² Mains Power Cable, Black Polyvinyl Chloride PVC Sheath 100m, 300 V, 500 V, 3183Y H05VV-F

RS Stock No.: 535-985



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

From RS PRO a high-quality medium duty H05VV-F harmonised flexible mains power cable with PVC insulation and a PVC jacket. This flexible cable has a voltage rating of 300 to 500 V and is designed for use in medium duty domestic and light industrial appliances

General Specifications

Туре	3183Y	
Harmonised Code	H05VV-F	
Sheath Material	Polyvinyl Chloride PVC	
neath Colour Black		
Applications	Computer and office equipment, Kitchen appliances such as toasters, Household appliances such as vacuum cleaners and washing machines, Radios and music centres, Table lamps and floor lamps, Hair dryers, Electrical cooking or heating apparatus	

Electrical Specifications

Voltage Rating	300 V, 500 V	
Insulation Material	PVC	
Conductor Material	Copper	



Mechanical Specifications

Length	100m
Cross Sectional Area	1 mm ²
American Wire Gauge	17AWG
Outer Diameter	8mm
Number of Cores	3
Conductor Strand Type	Stranded

Operation Environment Specifications

Operating Temperature Range	+5°C to +60°C
Minimum Operating Temperature	+5°C
Maximum Operating Temperature	+60°C

Approvals

Compliance/Certifications	2011/65/EU and 2015/863
Standards Met	RoHS Compliant





SIZE MM²	APPROX OVERALL DIAMETER MM	APPROX WEIGHT KG/KM
2 CORES		
0,75 1 1,5 2,5 4*	7,2 55 7,5 63 8,6 82 10,6 126 12,1 173	
3 CORES		
0,75 1 1,5 2,5 4*	7,6 8 9,4 11,4 13,1	65 76 104 160 220
4 CORES		
0,75 1 1,5 2,5 4*	8,3 9 10,5 12,5 14,3	78 96 130 194 270
5 CORES		
0,75 1 1,5 2,5 4*	9,3 9,8 11,6 13,9 16,1	97 115 160 238 350

^{*} Non HAR

Т					10.00
١			0	2	200
- 1		\sim	X	1 90	92
- 1					
- 1	H05 VV-F	brown-blue	brown-blue-G/Y	black-grev-brown-G/Y	grey-blue-brown-black-G/Y