

Pass & Seymour

Wall Plates Dustproof Stainless Steel Covers One & Two Gang

WP1, WP2, WP7, WP8, WPH8, WP26, WPH26, WP13, WP23, WPH1-L, WPH7-L, WPH8-L, WP26-L

Exceptional durability plus dust protection.

hese brushed stainless steel dust covers are designed to handle challenging conditions including dusty, corrosive environments, or hard-use areas. Yet they provide a smooth, handsome style that fits in anywhere. Note: these covers are not suitable for wet locations — see our Weatherproof Covers if water resistance is required.



Features & Benefits

Aesthetically pleasing design.

These stainless steel covers are dustproof only and do not meet NEC 406.8(A) or (B).



Field Uses/Vertical Markets

- IndustrialRetail
- Health Care
- Office

- Education
- Hospitality/Lodging
- Institutional
- Multiple Dwelling



Wall Plates Dustproof Stainless Steel Covers One & Two Gang

Ordering Information

Catalog Number		Description
One & Two Gang Dust Covers		
	WP1	Toggle Switch Small Cover, Vertical 1 Gang Plate Available for Box Mount – add suffix -FS.
	WP2	2 Toggle Switches 2 Small Covers, Vertical 2 Gang Plate
	WP7	Single Receptacle Small Cover, Vertical 1 Gang Plate Available for Box Mount – add suffix -FS.
	WP8	Duplex Receptacle Long Cover, Vertical 1 Gang Plate
•••	WPH8	Duplex Receptacle Long Cover, Horizontal 1 Gang Plate
	WP26	Decorator/GFCI Long Cover, Vertical 1 Gang Plate
	WPH26	Decorator/GFCI Long Cover, Horizontal 1 Gang Plate
	WP13	1 Gang Blank (Box Mounted) Gasketed
	WP23	2 Gang Blank (Box Mounted) Gasketed
Locking Dust Covers		
(a)	WPH1-L	Toggle Opening Horizontal
(a)	WPH7-L	Single Receptacle Opening Horizontal
	WPH8-L	Duplex Receptacle Opening Horizontal
	WP26-L	Decorator/GFCI Vertical
	WP255-K	Key for all Dustproof Locking Covers. (Two keys furnished with each unit.)

For more information on these and other P&S products refer to our Product Guide or visit our web site.

Wall Plates Dustproof Stainless Steel Covers One & Two Gang



Technical Specifications

3rd Party Compliance

UL Listed. CSA Certified.

Performance

Environmental Dustproof Only

Materials

Body .030" 302 Stainless Steel

Finish Brushed


Springs Stainless Steel 17-7 Screws 302 Stainless Steel

Gasket Vinyl


Lock Stainless Steel

Warranty

1 Year




Dimensions for WP1 & WP7



Dimensions for WP2



Dimensions for WPH8 & WPH26




Dimensions for Vertical Locking



Dimensions for Horizontal Locking



Dimensions for WP13



Dimensions for WP8 & WP26

Complementary Devices & Accessories



WALL PLATES

- TradeMaster® Thermoplastic Nylon
- Stainless Steel
- Brass
- Aluminum



WEATHERPROOF BOXES & COVERS

- While-In-Use Covers
- Heavy Cast Aluminum Covers
- Cast Covers
- Boxes



SWITCHES

- Heavy-Duty Toggle
- Heavy-Duty Lighted Toggle
- Heavy-Duty Security
- Heavy-Duty Locking
- Construction Grade Toggle
- Commercial Grade Toggle



STRAIGHT BLADE RECEPTACLES

- Extra Heavy-Duty
- Heavy-Duty
- Construction Grade
- Commercial Grade



GFCIs

- Construction Grade with Auto-Ground
- Construction Grade
- Construction Grade Dead Front

Also available...

- Light Almond Devices
- Decorator Devices
- Hospital Grade Devices
- PlugTail[™] Devices
- TVSS & Isolated Ground Devices
- Ground Continuity Monitoring (GCM)
- Straight Blade Plugs & Connectors
- Turnlok® Locking Devices
- IEC 309 Industrial Products
- Flexcor® Wire Mesh Grips
- Configurable Solutions



Legrand/Pass & Seymour P.O. Box 4822

Syracuse, NY 13221-4822 800-223-4185 North America Headquarters

60 Woodlawn Street West Hartford, CT 06110 Phone: 1.877.BY.LEGRAND (295.3472) Fax: 1.860.232.2062 www.legrand.us Legrand Canada 570 Applewood Crescent Vaughan, ON, L4K 4B4 Phone: 905.738.9195 Fax: 905.738.9721 www.legrand.ca