

Black nitrile exam gloves for dirt-masking hand protection and superior grip

- **Masks stains:** MICROFLEX® 93-852 exam gloves' black color disguises dirt while enhancing the visibility of light-colored objects
- **Enhanced grip:** A fully textured, non-foaming design ensures these powder- and silicone-free nitrile gloves have superior grip
- **Proven protection:** These medical exam gloves are approved for use against fentanyl and gastric acid (vomit), ensuring they are suitable for hazardous overdose situations — they also comply with EN ISO 374 Type B chemical resistance standards for chemical splash protection
- **Genuine versatility:** These gloves are suitable for various applications, used notably by auto mechanics, maintenance workers and law enforcement officers
- **Food handling compliant:** Also ideal for a wide range of food handling applications



Industries

- Automotive
- Automotive Aftermarket
- Life Sciences
- Machinery and Equipment

Recommended For

- Inspection, selecting, checking parts
- General Purpose Auto Aftermarket
- Use of cleaning tools and robotic equipment
- Oil, fluids and filter change
- Engine transmission and repair
- Tire rotation & changes
- Maintaining lab furniture and equipment
- Sample taking and processing
- Blending, compounding solids and liquids
- Raw material sample collection
- Weighing and dispensing of solid and liquid raw materials
- Inspection (picking, checking and marking)

TECHNICAL DATA SHEET

	Product Information
External Glove Surface	Fully Textured
Audit Standards	ISO 13485:2003
Product Certification	Medical Device Regulation (EU) 2017/745 Class I, Personal Protective Equipment Regulation (EU) 2016/425 Category III risks, CE 0493, EC 2023/2006, EC 1935/2004, EN 455 1-4, EN ISO 21420:2020, EN ISO 374-1:2016 Type B JKT, EN ISO 374-5:2016 Virus, ISO 11193, ISO 18889:2019, UKCA, EU Food Contact Approved
Packaging Overview	100 gloves per dispenser 10 dispensers per case 1000 gloves per case
Storage Instructions	Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition.
Country Of Origin	Malaysia
Product Segmentation	Robust
Antistatic	Yes EN1149
Silicone Free	Yes
Vulcanization Chemical Accelerators	- Zinc Diethyldithiocarbamate (ZDEC) - Zinc Dibutyldithiocarbamate (ZDBC) <i>Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.</i>

PHYSICAL PROPERTIES

	Typical Values		Testing Method
Length (mm/inches)	245 / 9.6		ASTM D3767,EN 420
Freedom from Holes (Inspection level I)	1.5 AQL		ASTM D5151,EN 455-2
Palm Thickness (mm/mils)	0.12 / 4.7		ASTM D3767,EN 420
Finger Thickness (mm/mils)	0.15 / 5.9		ASTM D3767,EN 420
	BEFORE AGING	AFTER AGING	
Ultimate Tensile Strength (MPa)	24	20	ASTM D412 & D573
Elongation at Break (%)	600	500	ASTM D412
Force at break (N)	7	6	EN 455-2

ORDERING INFORMATION

Size	XS (5.5 - 6)	S (6.5 - 7)	M (7.5 - 8)	L (8.5 - 9)	XL (9.5 - 10)	XXL (10.5 - 11)
Product Code	93852060	93852070	93852080	93852090	93852100	93852110

Performance Standards and Regulatory Compliance



For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region Ansell Healthcare Europe NV T: +32 (0) 2 528 74 00 F: +32 (0) 2 528 74 01 Asia Pacific Region MY +603 8310 6688 apac.medical@ansell.com CN: +86 21 38275000 infochina@ansell.com JP: +813 5549 8151 info.medical.jp@ansell.com	North America Region Ansell Healthcare Products LLC T: +1 800 800 0444 F: +1 800 800 0445 Latin America & Caribbean Region BR +55 (11) 3356-3100 latam.medical@ansell.com MX: +52 442 296 2050 latam.medical@ansell.com CO: +57 1 288 3247 latam.medical@ansell.com	Australia Ansell Limited T: +61 1800 337 041 F: +61 1800 803 578 Russia Ansell PYC Ten. +7 495 258 13 16
--	---	--

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

