

CZL10-12RA



CU 90DEGREE LUG 10SQMM M12



General Information

Extended Product Type	CZL10-12RA
Product ID	7TBH007940R0299
EAN	5415022378146
Catalog Description	CU 90DEGREE LUG 10SQMM M12
Long Description	Copper One-Hole Right Angle Metric Lug, Standard Barrel, Cable Size 10mm ² , Stud Size M12, Length 16mm, Flat 22.5mm, Hole Spacing 10mm

Ordering

EAN	5415022378146
Minimum Order Quantity	800 piece
Customs Tariff Number	8536904000

Dimensions

Product Net Weight	6.972 g
--------------------	---------

Container Information

Package Level 1 Width	102.108 mm
Package Level 1 Height	98.044 mm
Package Level 1 Depth / Length	72.898 mm
Package Level 1 EAN	00786210082264
Package Level 2 Units	800 piece
Package Level 2 Width	320.04 mm
Package Level 2 Height	220.98 mm
Package Level 2 Depth / Length	215.9 mm
Package Level 2 EAN	00786210082264
Package Level 3 Units	800 piece

Additional Information

Brand / Label	Spec-Kon
Insulation Material	None
Material	Copper
Product Main Type	COMPRESSION CONNECTORS

Product Name	COPPER LUG
Product Type	Copper One-Hole 90 Degree Metric Lug
UPC	786210082264

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	CZL10-12RA
Instructions and Manuals	CZL10-12RA

Classifications

ETIM 6	EC001051 - Tube cable lug for copper conductors
UNSPSC	39121405
WEEE Category	Product Not in WEEE Scope

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Compression & Mechanical Connectors

