



Plate Switches

Description

Metalclad offers a tough and impact resistant range of accessories with a durable finish and protective coating.

Each product is supplied in its own polybag, protecting it up to the point of installation.

Features

- Durable and tough finish with protective coating
- Supplied complete with surface mounting box with knockouts
- Captive and backed out terminals
- Terminals have clearly embossed markings
- Only one size 4mm screwdriver needed
- X-rated and can be used for switching inductive or fluorescent loads with de-rating
- Terminals have large lead-ins
- 25-year guarantee

Range

1 gang 2 way	VM1203
2 gang 2 way	VM1204
3 gang 2 way	VM1205

Technical Specification

Voltage rating	250Vac
Current Rating	10A
	X rated
Contact gap	3mm

No user serviceable parts

Back Boxes

All knockouts are 20mm diameter

	Sides	Back
1g	5	1

Standards

- BS EN 60669-1:2018

Terminal Capacity

	1mm ²	1.5mm ²	2.5mm ²	4mm ²
L	5	4	2	1