





ON 9MO




MODEL NO.
VQ220*⁻⁵*¹-XF


ENCLOSURE
NIL:DUST TIGHT
W :IP65(DUST TIGHT/LOW JETPROOF TYPE)

SEAL
0 :METAL SEAL
1 :RUBBER SEAL

SYMBOL



INDICATOR LIGHT &
SURGE SUPPRESSOR



SPECIFICATIONS

VALVE TYPE	5 PORT 2 POSITION AIR OPERATED VALVE	
VALVE CONSTRUCTION	METAL SEAL, RUBBER SEAL	
TYPE OF ACTUATION	DOUBLE SOLENOID	
FLUID	AIR	
OPERATING PRESSURE RANGE	METAL SEAL	0.1 TO 0.7MPa
	RUBBER SEAL	0.1 TO 0.7MPa
AMBIENT&OPERATING FLUID TEMPERATURE	-10 TO 50°C(NON FREEZE)	
VOLTAGE TOLERANCE	-10 TO 10%	

RATED VOLTAGE:24VDC

SPECIAL REQUIREMENT
NO POLARITY

NOTES

- UNLESS OTHERWISE NOTED ALONG WITH A SEPARATE CONTRACT OR AGREEMENT WITHIN THE PRODUCT SPECIFICATIONS, THE SAFETY INSTRUCTIONS SPECIFIED IN THE PRODUCT CATALOG ARE APPLIED.PLEASE CONTACT YOUR LOCAL SMC SALES OFFICE FOR FURTHER DETAILS.
- CE/UKCA MARKED PRODUCT.
[THE RELEVANT TCF IS AVAILABLE AS]
STANDARD PRODUCT SERIES.
- DIMENSIONS ARE IN MILLIMETERS.

				FINISH			
				PAINT			
				MASS			
				PACKING			
REV	QTY	DESCRIPTION	DATE PREPARED	REV NO	MATERIAL		MODEL QTY
TOLERANCES JIS B 0405				DRAWN	Y.ISHIZAWA	SCALE	
GRADE				DATE	2022-04-20	FREE	
RANGE (mm)				DESIGNED	M.KAWAI	DWG NAME	
0.5≤D≤3				DATE	2022-04-20	5 PORT SOLENOID VALVE	
3<D≤6				CHECKED		DWG NO	
6<D≤30				DATE		① VQ220 ⁰ ₁ -5(W)1-XF	REVISION
30<D≤120				APPROVED	T.FUJIWARA		2
120<D≤400				DATE	2022-04-21		
400<D≤1000							
1000<D≤2000							

FINISH:表面処理 / PAINT:塗装 / MASS:質量
PACKING:包装区分 / MATERIAL:材質
MATERIAL SIZE:材料寸法

DWG NAME PILOT VALVE:V100 SERIES

DWG REC

DWG ID BA24968602

SMC Corporation

ST