

## Han® S 120 FC CRT 25 mm<sup>2</sup>



Image is for illustration purposes only. Please refer to product description.

Part number	09 93 000 8262
Specification	Han® S 120 FC CRT 25 mm <sup>2</sup>
HARTING eCatalogue	<a href="https://harting.com/09930008262">https://harting.com/09930008262</a>

### Identification

Category	Contacts
Series	Han® S
Identification	Han® S 120
Type of contact	Crimp contact
Description of the contact	Female contact

### Version

Termination method	Crimp termination
Manufacturing process	Turned contacts
Details	Using of rubber sleeve is imperative! Please order separately.

### Technical characteristics

Conductor cross-section	25 mm <sup>2</sup>
Conductor cross-section [AWG]	AWG 4
Rated current	≤120 A
Contact resistance	≤0.3 mΩ
Stripping length	22 mm

### Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
RoHS	compliant
ELV status	compliant



**Pushing Performance**  
Since 1945

## Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

## Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
----------------	--------------------------

## Commercial data

Packaging size	1
Net weight	24.3 g
Country of origin	China
European customs tariff number	85366990
GTIN	5713140188761
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522