

ZCEA7

limit switch head ZCE - spring rod lever
thermoplastic end silicone boot



The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.



Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCE
Head type	Multi-directional head
Product compatibility	XCKP XCKD XCKT XCMD

Associated body	ZCMD21L1 ZCP35 ZCMD39L1 ZCMD37L2 ZCT25P16 ZCD21M12 ZCMD21C12 ZCD37 ZCMD29L2 ZCD28 ZCMD41L5 ZCMD81L5 ZCP21 ZCP39 ZCMD21L08R12 ZCMD81L1 ZCT26P16 ZCT27G11 ZCMD41L2 ZCMD39L5 ZCMD21L2 ZCT25N12 ZCD21 ZCP27 ZCD35 ZCD27 ZCT25G11 ZCP21M12 ZCMD61M12 ZCD31 ZCP31 ZCMD29C12 ZCP28 ZCT27N12 ZCT26G11 ZCT21P16 ZCMD21L5 ZCMD21L08U78 ZCMD29L1 ZCT21G11 ZCMD39L2 ZCMD61C12 ZCMD29L5 ZCMD41L1 ZCD29M12 ZCD25 ZCMD69C12 ZCMD81L2 ZCT27P16 ZCMD25L5 ZCP37 ZCP26 ZCT28P16 ZCMD25L1 ZCD29 ZCP25 ZCD39 ZCMD37L1 ZCT21N12 ZCMD25L2 ZCT28N12 ZCT28G11 ZCT26N12 ZCP29 ZCD26 ZCMD37L5 ZCP29M12 ZCMD21M12
Movement of operating head	Multi-directional
Type of operator	Spring rod spring return metal (with silicone boot and thermoplastic end)
Type of approach	Multi-directional approach

Complementary

Switch actuation	By any moving part
Positive opening	Without

Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment

Packing Units

Package 1 Weight	16 g
Package 2 Weight	197 g
Package 3 Weight	2.22 kg

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------