

Datasheet

RS Pro Eyebolt M24

RS Stock No: **673-670**



Product Details

RS Pro eyebolt with M24 thread size, is suitable for use in a wide range of lifting applications. This eyebolt is proof tested and supplied completely with test certificate. It is a high quality metric eyebolt with collar to BS4278. This eyebolt made of carbon steel, has a diameter of 15 mm.

Features and Benefits

- M10 thread size
- 15 mm thread length
- Made of carbon steel
- 2.5t working load limit



ENGLISH

Specifications:

Diameter	35 mm
Material	Carbon Steel
Thread Length	40 mm
Thread Size	M24
Working Load Limit	2.5 t
Collar Diameter	52 mm
Collar Thickness	17 mm
Eye Outside Diameter	77 mm
Overall Height	124 mm
Standards Met	BS 4278:1984