

# Endress+Hauser TMT84-A1A2C

## iTEMP TMT84, Transmitter PA



Dual sensor input. Advanced diagnostics: sensor monitoring. PROFIBUS PA Profile 3.02.

Picture for reference only. Product appearance may vary based on configuration

### Configuration of TMT84-A1A2C:

Approval:	A1	Non-hazardous area
Output Signal:	A	PROFIBUS PA
Electrical Connection:	2	Screw terminals, housing form B, DIN EN 50446
Field Housing:	C	W/o

Alternative part number: TMT84-25J0/0