

Eaton BAO40

Catalog Number: BAO40

Fuse-link, LV, 40 A, AC 500 V, BS88/A3, 21 x 87 mm, gL/gG, BS



General specifications

| | |
|--|------------------------------|
| Product Name | Catalog Number |
| Eaton Bussmann series low voltage British standard fuse | BAO40 UPC 051712838542 |
| EAN | Product Length/Depth |
| 5027590491976 | 87 mm |
| Product Height | Product Width |
| 21 mm | 21 mm |
| Product Weight | Warranty |
| 50.4 g | Not Applicable |
| Compliances | Certifications |
| CE Marked RoHS Compliant | IEC 60269-2 BS88 |

Electrical rating

Amperage Rating

40 A

Breaking capacity

80 kA

Interrupt rating

80 kAIC

Rated switching capacity

80 kA

Voltage rating

500 V

Voltage type

AC

Physical details

Color

None

Fuse type

BAO

General information

Class

Class gG/gL

Connection

74 mm Fixing Centre

Construction size

A3

Fitted with:

Offset bolted tags

Fuse indicator

None

Fuse shape

Offset bolted tags

Fuse size

BS88/A3

Insulated metal gripping lugs (IMGL)

No

Utilization category

gL/gG (cable protection/equipment protection)

Resources

Catalogs

CA134002EN

Compliance information

UKCA AAO,BAO,CEO,NITD,NIT,GTIS,CEO100M,GTIS63M

CE AAO,BAO,CEO,NITD,NIT,GTIS,CEO100M,GTIS63M

Multimedia

Eaton Bussmann - Red Spot fuse links

Technical data sheets



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)