



PRODUCT NUMBER: 6246163 Sprint S3 HI CI SRC

- 100 % metal free
- Low-cut style
- Leather upper and water-repellent textile
- Poromax® 3D moisture absorbent lining
- Non-metallic FLEXIUM™ anti-perforation interlayer
- ESD sole
- THERMY anti-bacterial treatment
- Dual density polyurethane outsole

WATCH VIDEO



Overview

Reference Number

6246163

Product Type

Footwear

Range

Bacou Original Free

Brand

Honeywell

Brand formerly known as

BACOU

Industry

- Administration
- Building and Construction
- Energy or Electricity
- General Industry
- Logistics
- Maintenance
- Services
- Transportation
- Utilities

Features & Benefits

Feature

Full grain leather

Benefit

Comfort, breathable and water repellent

Feature

Poromax® 3D lining

Benefit

Total absorption of moisture

Feature

Wear-off indicators

Benefit

Providing information on outsole abrasion level

Feature

High shock-absorption heel

Benefit

Comfort, Shock absorption and improved stability

Feature

Ergonomic sole Wave Concept

Benefit

Protection and comfort that flows, to allow a natural walking motion

Feature

Ultra-light composite safety toecap and overcap protection

Benefit

High level of stable performances and premium protection

Technical Description

Sizes

EU size available on stock from 35 to 49

Midsole

Non-metallic FLEXIUM™ anti-perforation interlayer

Upper

Breathable and water repellent full grain leather

Toe Cap

Non metallic 200J, Ultra-light composite safety toecap

Insole

Double density foam for a perfect shock absorption, Ergonomic, Antistatic, removable and antibacterial, Washable untill 90°C, Tear and abrasion resistance, Water absorption and desorption, Available in different width in order to adapt the fitting to users morphology

Outsole

Injected Double density PU outsole, slip resistant

Additional Features

- CI
- HI
- SRC

Certifications

EU Category PPE

2

Certifications

- EN ISO 20345:2011
- Other Regulation (EU) 2016/425

REACH

EU Regulation 1907/2006 (REACH) Compliance	
The substance(s) listed below may be contained in this product above the threshold level of 0.1% by weight of the listed article.	
Product Reference Sold in Europe	Substance > 0.1%
Substance Name	CAS Number
No Substance Content	

Additional Certification Link

6246163 SPRINT S3 HI CI SRC

