



Datasheet

RS PRO Double Sided Cotton Cloth Tape

19mm x 50m

Stock number: 2175251

EN



General Description

The tape is a cotton cloth coated on both sides with a clear, hot melt, plasticiser free, synthetic rubber based adhesive, interleaved with a yellow siliconised paper release liner. Suitable for many materials with uneven surfaces due to its high conformability and high level of adhesion. Ideal for permanent fitting of carpets and other floor coverings.

Features

- High tack
- Conformable to awkward shapes
- Easy tear
- Good adhesion

Technical Details	Typical Values
Thickness	0.25 mm
Breaking Load	22 N/cm
Elongation	4%
Adhesion to steel faced side	20.0 N/cm
Adhesion to steel unfaced side	20.0 N/cm
RoHS compliant	Yes
Service Temperature	-10°C to +50°C
Application Temperature	+10°C to +30°C
Storage Temperature	+12°C to +25°C

STORAGE

Tapes stored below the minimum recommended temperature will require warming up to that level before use. Up to 24 hours may be required for this to take place.

