



DWE4884

450W 6.35mm Slide Switch Die Grinder

Selling Proposition

- Long nose with rubber grip improves access, comfort and control
- Anti-lock collet ensures that all attachments are easily removeable once the nut is loosened
- Powerful 450W motor allows maximum performance in demanding applications
- Slim, ergonomic design results in user comfort allowing strain free grinding
- Low operating temperature increases user comfort in prolonged applications
- Ergonomic, lock-on slide switch for maximum flexibility
- Easy service, 1 screw design
- Cut-off brushes to prolong motor life
- Airstream directed away from user for improved comfort in use

Standard Equipment

- 6.35 mm collet
- Spanner

Warranty Specifications

- 30 Day No Risk Satisfaction Guarantee
- 1 Year Free Service Contract
- 3 Year Limited Warranty

Specifications	
Power Input	450 Watts
Power Output	
No Load Speed	25000 rpm
Collet Size	6 mm
Weight	1.6 kg
Length	356 mm
Height	0 mm
Spindle lock	No
Hand/Arm Vibration - Grinding	4.4 m/s ²
Uncertainty K 1 (Vibration)	1.9 m/s ²
Sound Pressure	80 dB(A)
Uncertainty K 1 (Sound)	3 dB(A)
Accoustic Pressure	91 dB(A)
Uncertainty K 2 (Sound)	3 dB(A)