

NSYPAP64G

reversible internal door polyester 2 locks grid pattern
forPLM64



Main

Range	Thalassa
Accessory / separate part category	Enclosure accessory
Product or component type	Door
Device application	Multi-purpose
For enclosure nominal dimensions	
Mounting location	Front side
Range compatibility	Thalassa PLM
Device composition	1 door 1 handle 4 fixing brackets

Complementary

Material	Polyester charged with fibreglass
Colour	Grey RAL 7035
Lock type	Lock 5 mm double bar
Number of locks	2
Door type	Internal plain
Door opening	Reversible 110 °
Height	Grid pattern : 515 mm
Width	Grid pattern : 305 mm
Depth	Available depth between enclosure door : 32 mm Available depth between rear : 194 mm

Environment

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Compliant - since 1511 - Schneider Electric declaration of conformity

Contractual warranty

Warranty period	18 months
-----------------	-----------