



ASP-AS-C39-JT-C

Coarse Cut Pole Pruning Saw 390 mm



PRODUCT DETAILS

- Product is suitable for the applications; pruning, trimming, gardening, arborist and forestry
- Precision ground, razor sharp JT teething provides smooth cutting and perfect result
- Strong blade with 5,4 TPI (coarse teething) for thicker branches where quick coarse cut is required
- Sheath in impact-resistant plastic with quick locking and thumb grip release and belt loop
- Easier cutting of branches at height with the precision ground, razor sharp Japanese teething when attached to section pole
- Reduced friction and concentrated cutting energy from the taper ground blade teething
- Hook at tip of blade to prevent slipping out of kerf
- Bark breaking blade at joint of the blade and adaptor
- The tooth tip hardened curved blade is flexible, yet stable and long lasting
- Connection adaptor for the ASP-1850 pole system, two alternative lengths, C39, 390 mm or C45, 450 mm



PRODUCT ATTRIBUTES

Product					
ASP-AS-C39-JT-C	390 mm	15-1/4 in	5.4	302 g	10.7 oz

Follow the Fish!

