

1838E

Rechargeable under bonnet LED lamp

CE

IP20

- Triple light emission: 500/1000/2000 lumens
 - Can be rotated 360°
 - Length range: 116 ÷ 188 cm
 - Aluminium body
 - Nonslip rubber hooks
 - USB-C charge
 - 2 charging modes:
charge via lamp USB port
charge via internal battery USB port
 - Supplied with battery charger
- Input: 100-240V ~ 50/60Hz
Output: DC 5V - 2000 mA

 1,12 kg

	art.						 kg
018380270	1838E	1170	1880	820	150	105	1,12

