


Technical data sheet

Article number:
170-01270

Twist-In-EMIPHYZ-05



Product Group	Self-closing, EMI protective sleeving
Product Family	Helagaine Twist-In-EMIPHYZ
Material	Tin-plated copper (SNCU), Polyester (PET)
Colour	Metal (ML), Orange (OG)
Application Method	For optimum cable protection including flexibility, we recommend that a filling level of 75% is not exceeded.
Bundle Ø max.	5 mm
Bundle Ø min.	1 mm
EMI requirements	Tested from 10 kHz to 100 MHz according to IEC 62153-4-3 (triaxial method) Results on request
Operating Temperature	-40 °C to +150 °C
Package Content	150 m
Package Content packed in	reel
Specifications	EN 45545-2
Weight	41 g/m

HF ✓

RoHS ✓

EN 45545-2